


Cartridge Valves Technical Information Motor Mount HICs MM-OMH-00-SVP10-NCR

OPERATION


This is a bypass solenoid HIC with drain that mounts to DH motors with manifold mount porting. When energized, the valve connects ports A and B. Drain connects to port A.



SPECIFICATIONS

Theoretical performance Pressure drop

33 cSt [154 SUS] hyd.oil @ 38°C [100° F]




Specifications

Rated pressure	210 bar [3045 psi]
Rated flow at 7 bar	80 l/min [21 US gal/min]
[102 psi]	
Leakage	6 drops/min @ at rated
	pressure
Weight	1.51 kg [3.33 lb]
Cartridge	SVP10-NCR
Shuttle/drain port	#4 SAE (1/4 BSP)
Service mount kit	11023869
Motor	ОМН

DIMENSIONS


Cross-sectional view

mm [in]



ORDERING **INFORMATION**

MM-OMH-00-BSVP10-NCR-12D-DE-B-N-10S



* These terminations not available on robust coil (R12D, R24D)

P104 750