



a | 12.01.10 | KOR/BRE | part-no. added / new chassis  
 | date | name | amendment

Dimensions toleranced according to ISO 2768-m						
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8

drawn	10.12.09	Kornau	Kornau	scale	1:4
checked	10.12.09	Bremer	Bremer	format	A4
	date	name	signature		

Dimensions B 0908110  
 du/dt filter 40A – IP00

DIN ISO 5456		order number	drawing number	modi.	sheet
		130B2835	Z790911010	a	1/1
all dimensions mm		Please observe protection clause to DIN 34			