



a	13.01.10	KOR/LAU	part-no.	added
	date	name	amendment	

Dimensions toleranced according to ISO 2768-m						
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	± 0.1	± 0.1	± 0.2	± 0.3	± 0.5	± 0.8

drawn	18.11.09	Kornau	Kornau	scale	1:4,5
checked	18.11.09	Bremer	Bremer	formate	A4
	date	name	signature		
				DIN ISO 5456	
				all dimensions mm	

Dimensions B 0908114
du/dt filter 303A – IP00

order number	drawing number	modi.	sheet
130B2847	Z790911018	a	1/1

Please observe protection clause to DIN 34