






additional informations:

filter colour : impregnated
 filter weight : 410kg

label:

VLT MCC 101 sine wave FILTER www.danfoss.com	
T/C: MCC101A660T5E00	S/N: 000165-390
P/N: 130B3191	3x 380-500V - 50/60Hz (max 100Hz)
3x 660A	
Pluss: 2000W	L=150µH
Chassis/IP00	Tamb 45°C/113°F
130B3191000165-390	
E 219022 UL US Ind. Contr. Eq.	B 1001077 FA-Nr.: 000000
VDE 0570 EN 61558	MADE IN GERMANY



a	30.09.10	KOR/Lauer	approval added
	date	name	amendment

Dimensions toleranced according to ISO 2768-m						
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8

drawn	01.06.10	Kornau	Kornau	scale
checked	01.06.10	Bremer	Bremer	format
	date	name	signature	A4
				DIN ISO 5456
				all dimensions mm

Dimensions B 1001077				
sine-wave filter 500V 660A - IP00				
order number	130B3191	drawing number	Z791004007	modi.
				a
sheet	1/1	Please observe protection clause to DIN 34		