





additional informations:
 filter colour : zinc plated steel
 filter weight : 11,2kg

label:

VLT ® MCC 101 sine wave FILTER www.danloss.com		MADE IN GERMANY L&L GmbH Postfach 33104 Pöps: 104W Weight: 11,2kg Tightening torque terminal: 0,5-1,0Nm	
T/C: MCC101A10KTE08 S/N: 000148-083 P/N: 130B7289 3x 10A Chassis IP00 Tamb: 45°C/113°F 130B728900148-083		B 1212047 FA#: 000000 EN 61558 CE	



Dimensions toleranced according to ISO 2768-m					
Tolerance class	0.5	from 3	from 6	from 30	from 120
	to 3	to 6	to 30	to 120	to 400
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5

drawn	19.02.13	Kornau	Kornau	scale	1:4
checked	19.02.13	Bremer	Bremer	format	A4
date		name		signature	
DIN ISO 5456		all dimensions mm		order number	
130B7289		drawing number		Z791302003	
modi:		0		sheet	
1/2		Please observe protection clause to ISO 16016		Dimensions B 1212047	
sine wave filter 690V 10A - IP00					

1 2 3 4 5 6 7 8

1 2 3 4 5 6 7 8

1 2 3 4 5 6 7 8

1 2 3 4 5 6 7 8





1 2 3 4 5 6 7 8

1 2 3 4 5 6 7 8

1 2 3 4 5 6 7 8

1 2 3 4 5 6 7 8

1 2 3 4 5 6 7 8



included accessories
(screen connection plate)

Dimensions toleranced according to ISO 2768-m							
Tolerance class	0.5	from 3	from 6	from 30	from 120	from 400	from 400
	to 3	to 6	to 30	to 120	to 400	to 1000	
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8	

drawn	19.02.13	Kornau	Kornau	scale	Dimensions B 1212047		
checked	19.02.13	Bremer	Bremer	1:4	sine wave filter 690V 10A – IP00		
	date	name	signature	formate	order number	drawing number	modi.
				A4	130B7289	Z791302003	0
				DIN ISO 5456	Please observe protection clause to ISO 16016		
				all dimensions mm			

