



NOTE: ALL WIRES ARE #16 AWG RED UNLESS OTHERWISE NOTED

	3		
	2		
	1		
RELEASE	0	SP14067	11/05/14
DESCRIPTION	REV	ECN	DATE

- NOTICE -

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF DANFOSS DRIVES. IT IS LOANED BY DANFOSS DRIVES SUBJECT TO THE CONDITIONS THAT IT AND THE INFORMATION EMBODIED THEREIN SHALL BE USED ONLY FOR RECORD AND REFERENCE PURPOSES, SHALL NOT BE USED OR CAUSED TO BE USED IN ANY WAY PREJUDICIAL TO THE INTERESTS OF DANFOSS DRIVES, SHALL NOT BE REPRODUCED OR COPIED IN WHOLE OR IN PART, OR DISCLOSED TO ANYONE WITHOUT THE DIRECT WRITTEN PERMISSION OF DANFOSS DRIVES AND SHALL BE RETURNED UPON REQUEST.

DRN	SJG	TOLERANCE	NAME		CONTROL WIRING DIAGRAM	
	APR	Unless Otherwise Specified	PHD PANEL HVAC SOFT-START BYPASS 460/575 VAC		. CB DISC., TYPE 3R, WITH DV/DT FILTER	
	SJG	2 PLC ±.02 3 PLC ±.005	MODEL	FC102	SHEET 2 OF 2	SIZE D
		SCALE 1.0			DWG. NO.	174N9972

