





NOTE: ALL WIRES ARE #16 AWG RED UNLESS OTHERWISE NOTED

**- NOTICE -**

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF DANFOSS DRIVES. IT IS LOANED BY DANFOSS DRIVES SUBJECT TO THE CONDITIONS THAT IT AND THE INFORMATION EMBODIED THEREIN SHALL BE USED ONLY FOR RECORD AND REFERENCE PURPOSES, SHALL NOT BE USED OR CAUSED TO BE USED IN ANY WAY PREJUDICIAL TO THE INTERESTS OF DANFOSS DRIVES, SHALL NOT BE REPRODUCED OR COPIED IN WHOLE OR IN PART, OR DISCLOSED TO ANYONE WITHOUT THE DIRECT WRITTEN PERMISSION OF DANFOSS DRIVES AND SHALL BE RETURNED UPON REQUEST.

	3		
	2		
	1		
RELEASE	0	SP14067	11/05/14
DESCRIPTION	REV	ECN	DATE

DRN	SJG	TOLERANCE	NAME		CONTROL WIRING DIAGRAM	
APR	SJG	Unless Otherwise Specified	PHD PANEL HVAC 3-CONTACTOR BYPASS 460/575 VAC		CB DISC., TYPE 3R	
		2 PLC. ±.02 3 PLC. ±.005	MODEL	FC102	SHEET 2 OF 2	SIZE D
		SCALE 1.0			DWG. NO.	174N9999

