

Ordering no.: 176F4709

FC 302 N90K T5 + FC 202 N110 T4 + FC 102 N110 T4

FC 302 N110 T5 + FC 202 N132 T4 + FC 102 N132 T4

FC 302 N132 T5 + FC 202 N160 T4 + FC 102 N160 T4

Description	Code no.	Qty.
Control Card, FC 302 with safe stop	130B1109	1
Control Card, FC 102 with safe stop	130B1150	1
Control Card, FC 202 with safe stop	130B1167	1
Current Scaling	176F3153	1
Current Scaling	176F3154	1
Current Scaling	176F3155	1
Balance/HF Card	176F3161	1
DC Bus Capacitor	176F3163	6
Heatsink Fan	176F3164	1
Mixing Fan	176F3165	1
IP20 Top Fan	176F3166	1
IP21/54 Door Fan	176F3168	1
Mains Fuse	176F3170	3
Mains Fuse	176F3171	3
Mains Fuse	176F3172	3
IGBT Gate Drive Cable	176F3175	3
IGBT Temperature Cable	176F3177	1
Brake IGBT Gate Drive Cable	176F3179	1
SCR Gate Drive Cable	176F3333	1
Bus Bar Assembly	176F3350	1
Door Fan Filter	176F3353	1
IGBT Module (300 amp)	176F3362	3
IGBT Module (450 amp)	176F3363	3
Brake IGBT Module (450 amp)	176F3366	1
Door Vent Kit	176F3375	1
Power Card Rugged NO 110kW 380-500V	176F3503	1
Power Card Rugged NO 132kW 380-500V	176F3504	1
Power Card Rugged NO 160kW 380-500V	176F3505	1
Power Card Rugged NO 110kW 380-480V	176F3509	1
Power Card Rugged NO 132kW 380-480V	176F3510	1
Power Card Rugged NO 160kW 380-480V	176F3511	1
Gate Drive Card Rugged NO 110-315kW 400V	176F3515	1
Inrush Card Rugged NO 110-315kW 400V	176F3517	1
SCR/Diode	176F8318	3
Snubber Capacitor	176F8323	3
Cable Control Card to Power Card D1h D3h	176F3183	1
Current Sensor	176F8342	3
Container	175Z2809	1