

Description	Value
<b>General information:</b>	
Product name:	UPML AUTO 25-105 180
Product No:	59C80053
EAN number:	5711495866433
Price:	
<b>Technical:</b>	
Maximum head:	105 dm
TF class:	95
Approvals:	CE,VDE
<b>Materials:</b>	
Pump housing:	Cast iron
Impeller:	PES 30% GF
<b>Installation:</b>	
Maximum ambient temperature:	55 °C
Maximum operating pressure:	10 bar
Port-to-port length:	180 mm
<b>Liquid:</b>	
Pumped liquid:	Water
Liquid temperature range:	-10 .. 95 °C
Selected liquid temperature:	60 °C
Density:	983.2 kg/m <sup>3</sup>
<b>Electrical data:</b>	
Power input - P1:	12 .. 140 W
Mains frequency:	50 Hz
Rated voltage:	1 x 230 V
Maximum current consumption:	0.1 .. 1.1 A
Enclosure class (IEC 34-5):	X2D
Thermal protec:	ELEC
<b>Others:</b>	
Energy (EEI):	0.23
Net weight:	2.56 kg
Gross weight:	2.7 kg

