

Type	Value
Max Weight	2.8 kg / 6.2 lb
IP Class	IP20 A
Nema Class	CHASSIS

B

C






D

E


F

G


H




DETAIL B  
SCALE 1:1



DETAIL A  
SCALE 1:1



MOUNTING BASE



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.  
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

● CENTER OF GRAVITY:  
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ±1MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]		FIRST ANGLE PROJECTION	SCALE	DRAWING SIZE	MATERIAL				
			1:2	A2	FINISH				
CHANGED						DESCRIPTION			
DESIGNED	DANFOSS 27-11-2015					MCAD A1 IP20 A			
CHECKED		DRAWING NUMBER							
		MCAD-A1-IP20-A							
		REV							
		001							
		SHEET							
		1 OF 1							
		PROPERTY OF DANFOSS A/S NORDBOG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.							
		MODEL							
		MCAD-A1-IP20-A							