









Type	Value
Max Weight	4.9 kg / 10.8 lb
IP Class	IP20 AC
Nema Class	CHASSIS



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY:
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ± 1 MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]		FIRST ANGLE PROJECTION	SCALE	DRAWING SIZE	MATERIAL				
			1:2	A2	FINISH				
CHANGED						DESCRIPTION			
DESIGNED	DANFOSS 27-11-2015					MCAD A2 IP20 AC			
CHECKED		DRAWING NUMBER							
		MCAD-A2-IP20-AC			REV				
		MCAD-A2-IP20-AC			001				
		MODEL			SHEET				
					1 OF 1				
PROPERTY OF DANFOSS A/S NORDBOG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.									