








Type	Value
Max Weight	6.6 kg / 14.6 lb
IP Class	IP20 B
Nema Class	CHASSIS



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT. SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY: FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ± 1 MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]		FIRST ANGLE PROJECTION	SCALE 1:2	DRAWING SIZE A2	MATERIAL	
					FINISH	
					DESCRIPTION	
CHANGED					MCAD A3 IP20 B	
DESIGNED	DANFOSS 09-01-2016					
CHECKED				DRAWING NUMBER	REV	
				MCAD-A3-IP20-B	001	
				MODEL	SHEET	
				MCAD-A3-IP20-B	1 OF 1	