









Type	Value
Max Weight	6.6 kg / 14.6 lb
IP Class	IP20
Nema Class	CHASSIS



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY:
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ± 1 MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]		FIRST ANGLE PROJECTION	SCALE	DRAWING SIZE	MATERIAL	
			1:2	A2		
					FINISH	
					DESCRIPTION	
					MCAD A3 IP20	
CHANGED		DRAWING NUMBER		REV		
DESIGNED	DANFOSS 09-01-2016	MCAD-A3-IP20		001		
CHECKED		MODEL		1 OF 1		
		MCAD-A3-IP20				
PROPERTY OF DANFOSS A/S NORDBOG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.						