








Type	Value
Max Weight	?? kg / ?? lb
IP Class	IP55/66
Nema Class	Type 12/4X



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT. SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

**CENTER OF GRAVITY:**  
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS $\pm 1$ MM (0,4 INCH). ALL DIMENSIONS ARE IN MILLIMETERS (INCH)		FIRST ANGLE PROJECTION	SCALE 1:5	SIZE A3	MATERIAL
CHANGED			DESCRIPTION  <b>MCAD A5 IP66 DISCONNECTOR</b>		
DESIGNED	Danfoss				
CHECKED					
PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.					DRAWING NUMBER <b>MCAD-A5-IP66-DISCONNECTOR</b> MODEL <b>MCAD-A5-IP66-DISCONNECTOR</b>
					REV SHEET <b>1 OF 1</b>