









Type	Value
Max Weight	45 kg / 99.21 lb
IP Class	IP21/55/66
Nema Class	Type 1/12/4X



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.  
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY:  
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ±1MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]		FIRST ANGLE PROJECTION	SCALE	DRAWING SIZE	MATERIAL
			1:5	A2	
		FINISH			
		DESCRIPTION			
		MCAD C1 IP66 WITH DISCONNECTOR			
CHANGED		DRAWING NUMBER			REV
DESIGNED	DANFOSS	MCAD-C1-IP66-WITH-DISCONNECTOR			001
CHECKED		MODEL			1 OF 1
		PROPERTY OF DANFOSS A/S NORDBOG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.			