

1 2 3 4 5 6 7 8 9 10 11 12

Type	Value
Max Weight	50 kg / 110.2 lb
IP Class	IP20 OPTION
Nema Class	CHASSIS

A

A

B

B

C

C

D

D

E

E

F






F

G


G

H


H




SCALE 1:5



DETAIL A  
SCALE 1:1



DETAIL B  
SCALE 1:1



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT. SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY: FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS $\pm 1$ MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]		FIRST ANGLE PROJECTION	SCALE	DRAWING SIZE	MATERIAL
			1:5	A2	
		FINISH			
		DESCRIPTION			
CHANGED					
DESIGNED	DANFOSS 25-04-16				
CHECKED					
PROPERTY OF DANFOSS A/S NORDBOG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.		DRAWING NUMBER		REV	
		MCAD-C4-IP20-OPTION		001	
		MODEL		SHEET	
		MCAD-C4-IP20-OPTION		1 OF 1	