


| | | | |
|-----------|----|--------|--------|
| $\phi 80$ | j6 | +0.012 | 80.012 |
| | | -0.007 | 79.993 |
| $\phi 19$ | j6 | +0.009 | 19.009 |
| | | -0.004 | 18.996 |
| DIMENSION | | FIT | |

| | | | |
|---|--|-----------------|--------------------|
| Type of document CUSTOMER DRAWING | Designed 12.07.2018 | | |
|  | Designation ISD 510, Size 2, 2.9 Nm | | |
| | Number MCAD-ISD-510-SIZE2-2.9 | Revision 001 | |
| Size A3 | Scale 1:2 | Sheet 1 | No. of Sheets 1 |

Unless otherwise specified the tolerance is 1 mm.
All dimensions are in mm.

Property of Danfoss A/S, Nordborg, Denmark.
Two or three dimensional reproduction of contents to be authorized by Danfoss A/S.