



Parameter list

Parameter	Description Beschreibung	Value Wert
5-40	Ready	2
5-12	Without function	0

*
 Current input, 0-20mA and 4-20mA
 Stromeingang, 0-20 mA und 4-20 mA
 Voltage input, -10 - +10 V DC
 Spannungseingang -10 - +10 V DC