



Parameter list

Parameter	Beschreibung	Value Wert
5-40	Ready	2
5-12	Without function	0

\* Current input, 0-20mA and 4-20mA  
 Stromeingang, 0-20 mA und 4-20 mA  
 Voltage input, -10 - +10 V DC  
 Spannungseingang -10 - +10 V DC

Modification	Date	Name	Contr.

Commission	9/30/2013	315KW VFD Panel
Project description		Disconnect switch+Fuse+dudt Filter
		Trennschalter+Sicherung+dudt Filter

Danfoss GmbH  
 VLT Drives EMA, Carl-Legien Strasse 8  
 63073 Offenbach, Germany



FILE-NAME: LOG08300.jpg Size 300px x 116px
--

Page description  
 Frequency converter  
 Frequenzumrichter

Project Number	----
SAP NO	

= FC302
+ P315KW 230V
Manufacturer no