



7.5:E U1-32
7.5:E U1-37

* Set point Sollwert

4.7:C U1-01
4.7:D U1-02

Drive signal start active [123]
FU Signal Start aktiv [123]

* Current input, 0-20mA and 4-20mA
Stromeingang, 0-20 mA und 4-20 mA
Voltage input, -10 - +10 V DC
Spannungseingang -10 - +10 V DC

4		Date	9/30/2013	Commission	Danfoss GmbH		Project Number		= FC302		Page
		Ed.	RAMKUMAR	160KW VFD Panel		VLT Drives EMA, Carl-Legien Strasse 8		MC_- - -		+ N160KW 230V	
		Appr	FALCO	Contactor+Fuse+dudt Filter		36073 Offenbach, Germany		SAP NO		Manufacturer no	
Modification		Date	Name	Contr.	KARTHIK	Schütz+Fuse+dudt Filter		Page description		Page	
								Frequency converter		5	
								Frequenzumrichter		30	



FILE-NAME:
LOG08300.jpg
Size 300px x 116px