



* Set point Sollwert

Drive signal start active [123]
FU Signal Start aktiv [123]

* Current input, 0-20mA and 4-20mA
Stromeingang, 0-20 mA und 4-20 mA
Voltage input, -10 - +10 V DC
Spannungseingang -10 - +10 V DC

4		Date		9/30/2013	Commission		Danfoss GmbH		Project description		Page description		Project Number		= FC302		Page		
		Ed.		RAMKUMAR	400KW VFD Panel		VLT Drives EMA, Carl-Legien Strasse 8		LOGO8300.jpg		Frequency converter		MC_ - - - -		+ P400KW 230V		5		
		Appr		FALCO	Contactor+Fuse+dudt Filter		36073 Offenbach, Germany		Size 300px x 116px		Frequenzumrichter		SAP NO		Manufacturer no		30		
Modification		Date		Name		Contr.		KARTHIK		Schütz+Fuse+dudt Filter									