



Power Standards Laboratory  
www.PowerStandards.com  
980 Atlantic Ave #100  
Alameda, CA 94501 USA  
TEL ++1-510-522-4400  
FAX ++1-510-522-4455

# SEMI F47-0706

(Reapproved 0812)

## Voltage Sag Immunity Compliance Certificate

### Adjustable Frequency Drive Model: VLT® Automation Drive series FC-300 (See Annex 1 for a more detailed model description)

**Description:** Adjustable Frequency Drive  
**Manufacturer Name:** Danfoss Drives A/S  
**Manufacturer Address:** Design Center EU, Ulsnaes 1, DK 6300 Graasten, Denmark  
**Test Date and Location:** 21 March 2017, same as above  
**Tested configuration:** Normal operation and motor load connection

**Pass/Fail criteria:** All electrical connections active and no error messages during all voltage sags

**Certification:**  
Power Standards Laboratory certifies that the above drive meets the requirements of SEMI F47-0706 for voltage sag immunity when tested according to the procedures set forth in IEC 61000-4-34. This project was covered under the PSL TestingPartner Program for Danfoss Drives A/S. This certificate is based on certificate DAN-20B. No changes have been done since.



Adjustable Frequency Drive  
(Representative model)



A handwritten signature in blue ink, appearing to read 'Andreas Eberhard'.

---

Andreas Eberhard                      23 June 2020  
Power Standards Lab

## ANNEX 1

### Detailed description of FC300 Drive Series

Type	IP20	IP21	IP55/66	Mains Supply [Vac]	Power [kW]
FC300 k25	X		X	200-240	0.25
FC300 k37	X		X	200-240/380-500	0.37
FC300 k55	X		X	200-240/380-500	0.55
FC300 k75	X		X	200-240/380-500/525-600	0.75
FC300 1k1	X		X	200-240/380-500/525-600/525-690	1.1
FC300 1k5	X		X	200-240/380-500/525-600/525-690	1.5
FC300 2k2	X		X	200-240/380-500/525-600	2.2
FC300 3k0	X		X	200-240/380-500/525-600	3
FC300 3k7	X		X	200-240	3.7
FC300 4k0	X		X	380-500/525-600/525-690	4
FC300 5k5	X	X	X	200-240/380-500/525-600/525-690	5.5
FC300 7k5	X	X	X	200-240/380-500/525-600/525-690	7.5
FC300 11k	X	X	X	200-240/380-500/525-600/525-690	11
FC300 15k	X	X	X	200-240/380-500/525-600/525-690	15
FC300 18k	X	X	X	200-240/380-500/525-600/525-690	18.5
FC300 22k	X	X	X	200-240/380-500/525-600/525-690	22
FC300 30k	X	X	X	200-240/380-500/525-600/525-690	30
FC300 37k	X	X	X	200-240/380-500/525-600/525-690	37
FC300 45k	X	X	X	380-500/525-600/525-690	45
FC300 55k	X	X	X	380-500/525-600/525-690	55
FC300 75k	X	X	X	380-500/525-600/525-690	75
FC300 90k	X	X	X	380-500/525-690	90