

Description	Value
<b>General information:</b>	
Product name:	UPM3 AUTO 15-70 130 ZZZ
Product No:	
EAN number:	
Price:	
<b>Technical:</b>	
Maximum head:	70 dm
TF class:	110
Approvals:	CE,VDE
<b>Materials:</b>	
Pump housing:	Cast iron
Impeller:	PES 30% GF
<b>Installation:</b>	
Maximum ambient temperature:	70 °C
Maximum operating pressure:	10 bar
Port-to-port length:	130 mm
<b>Liquid:</b>	
Pumped liquid:	Water
Liquid temperature range:	2 .. 110 °C
Selected liquid temperature:	60 °C
Density:	983.2 kg/m <sup>3</sup>
<b>Electrical data:</b>	
Power input - P1:	5 .. 52 W
Mains frequency:	50 Hz
Rated voltage:	1 x 230 V
Maximum current consumption:	0.07 .. 0.52 A
Enclosure class (IEC 34-5):	IP44
Thermal protec:	ELEC
<b>Controls:</b>	
Pos term box:	9H
<b>Others:</b>	
Energy (EEI):	0.20
Net weight:	1.76 kg
Gross weight:	2.12 kg

