



## NMMS.E134261 Power Conversion Equipment

If you notice a change to your NMMS Listing Card, click [here](#) to learn more.

[Page Bottom](#)

### Power Conversion Equipment

[See General Information for Power Conversion Equipment](#)

#### DANFOSS POWER ELECTRONICS A/S

E134261

ULSNAES 1

6300 GRAASTEN, DENMARK



Trademark and/or Tradename: "E134261" , "VLT" , "www.danfoss.com" ,

#### Investigated to ANSI/UL 508C

**AC Drive** Model(s) NBU-302/NBU-301/NBU-101/NBU-102/NBU-103, NBU-201, NBU-202, NBU-322

**AC motor controllers, "BFU Type"** Model(s) E05\*, E07\*, E11\*, E15\*, E22\*, E30\*, E40\*

**AC motor controllers, "CRB Type 400V"** Model(s) CRB 307, 315, 330

**AC motor controllers, "FCD Series"** Model(s) FCD302, followed by PK37, PK55, PK75, P1K1, P1K5, P2K2, or P3K0 followed by T4, followed by B, or W, followed by 66 or 69, followed by H1, followed by X or S, followed by X, Y, 1, or 3, followed by X, E, or F, followed by M, N, O, or X, followed by X, E, F, S, M, L or K, followed by X or C, followed by X, E, or F, followed by X, followed by X, followed by X, E, or P followed by X, followed by A, followed by X, 0, L, 8, Y, or N, followed by B, followed by X, R, Z, or U, followed by XXXXX or S067X followed by D, followed by X or 0.

**AC motor controllers, "FCD Type 400V"** Model(s) 303, 305, 307, 311, 315, 322, 330, 335, 340

**AC motor controllers, "PMX Type"** Model(s) C0-7\*, C00\*, C003\*, C1-1\*, C1-5\*, C2-2\*, C3-7\*

**AC motor controllers, "VLT Type"** Model(s) +2803\*, +2805\*, +2807\*, +2811\*, +2815\*, +2822\*, +2830\*, +2840\*, +2855\*, +2875\*, +2880\*, +2881\*, +2882\*

**AC motor controllers** Model(s) 176L8221, 176L8222, 176L8223, 176L8224, 176L8225, ADS102, AKD102, CD-302, CDS-302, CDS303

CPE134 or CPE135, followed by, P1k5, P2k2, P3k0, P4k0 followed by S2 or T2 or T4, followed by V03, followed by H3, followed by X, followed by Y, followed by X, followed by X, followed by X, followed by X or S, followed by SXXX, followed by X, followed by AX, followed by BX, followed by CX, followed by X, followed by XX, followed by DX..

CU-331, DV-302, FC-103

FC-302, FC-301, FC-101, FC-102, FC-103, FC-201, FC-202, PNR202, IR-301, IRV302, ADS102, MWU302, CD-302, CDS302, CDS303, LD-302, AKD102, CUE202, IVS102, BXX301, BXX302, TR-200, ITT102, FWX301, FC-322, DV-302, KSB202, NBU302, NBU301, NBU101, NBU102, NBU103, NBU201, NBU202, NBU322., WI-EFC, WLD302.

FC302, FC101, FC322, IPC102, IR302, IRV-302, ITT102, LD302/MWU302/CUE202, PNR202, TR-200, Type 1, Type 12, Type 4X Enclosure, WI-EFC, WLD-302

**AC motor controllers, 24 V External supply options** Model(s) 130B1108/130B1208@

**AC motor controllers, DC to DC Converters** Model(s) 130B1120/130B1209@

**AC motor controllers, Device net communication card options** Model(s) 130B1102/130B1202@

**AC motor controllers, Encoder options** Model(s) 130B1115/130B1215@

**AC motor controllers, MCA 101 Profibus DP V1 options** Model(s) 130B1100/130B1200

**AC motor controllers, MCA 104 DeviceNet options** Model(s) 130B1102/130B1202

**AC motor controllers, MCA 105 Canopen options** Model(s) 130B1103/130B1205

**AC motor controllers, MCA 107AKD LonWorks** Model(s) 130B1169/130B1269

**AC motor controllers, MCA 108 Lonworks options** Model(s) 130B1106/130B1206

**AC motor controllers, MCA 109 BacNet options** Model(s) 130B1144/130B1244

**AC motor controllers, MCA 113 Profibus conv.** Model(s) 130B1245

**AC motor controllers, MCA 114 Profibus conv.** Model(s) 130B1246

**AC motor controllers, MCA 115 TR200 LonWorks** Model(s) 130B1467

**AC motor controllers, MCA 121 Ethernet IP options** Model(s) 130B1119/130B1219

**AC motor controllers, MCA 122 Modbus TCP** Model(s) 130B1196/130B1296/130B7344

**AC motor controllers, MCB 101 General purpose I/O** Model(s) 130B1125/130B1212

**AC motor controllers, MCB 102 CL Encoder** Model(s) 130B1115/130B1203

**AC motor controllers, MCB 103 Resolver** Model(s) 130B1127/130B1227

**AC motor controllers, MCB 105 Relay card options** Model(s) 130B1110/130B1210

**AC motor controllers, MCB 107 24 V External supply options** Model(s) 130B1108/130B1208

**AC motor controllers, MCB 108 Safety PLC interfaces** Model(s) 130B1120

**AC motor controllers, MCB 109 Analog I/O options** Model(s) 130B1143/130B1243

**AC motor controllers, MCB 110 Real time clocks** Model(s) 130B1142/130B1242

**AC motor controllers, MCB 112 PTC Thermistor card options** Model(s) 130B1137

**AC motor controllers, MCB 113 Extended relay cards** Model(s) 130B1164/130B1264

**AC motor controllers, MCB 114 Sensor input kits MCB 115 programmable I/O options** Model(s) 130B1166/130B1266/130B1267

**AC motor controllers, MCB 116 TR-200 Real time clocks** Model(s) 130B7463/130B7464/130B7465

**AC motor controllers, MCB RTC Options** Model(s) 130B1120

**AC motor controllers, MCB105 Relay cards option B** Model(s) 130B1110

**AC motor controllers, MCO 102 Adv. Cascade controller options** Model(s) 130B1154/130B1254

**AC motor controllers, MCO 305 SyncPos programmable motion controls** Model(s) 130B1134/130B1234

**AC motor controllers, MCO 350 Synchronizing control options** Model(s) 130B1152/130B1252

**AC motor controllers, MCO 360 VLT SALT control options** Model(s) 130B7611/130B7612

**AC motor controllers, option kits** Model(s) Graphic Display Kit for panel mounting 130B1113

**AC motor controllers, option panel mounting kits (w/o additional display)** Model(s) Type 4X 130B1117

**AC motor controllers, options** Model(s) MCB 122 Encoder Ringspinner, MCB 132 Encoder Positioning, MCB 133 Resolver Positioning, MCO 101 Extended Cascade Control, MCO 104 Electronic Controlled Bypass, MCO 302 Motion Control API, MCO 351

**AC motor controllers, options, MCB105 Relay card option B (2A/250 Vac)** Model(s) 130B1110/130B1210

**AC motor controllers, Positioning control options** Model(s) 130B1153/130B1253

**AC motor controllers, Type 1/IP21 top enclosure kit B3 enclosure option kits** Model(s) 130B1187

**AC motor controllers, Type 1/IP21 top enclosure kit B4 enclosure option kits** Model(s) 130B1189

**AC motor controllers, Type 1/IP21 top enclosure kit C3 enclosure option kits** Model(s) 130B1191

**AC motor controllers, Type 1/IP21 top enclosure kit C4 enclosure option kits** Model(s) 130B1193

**AC motor controllers, Type 1/IP21 top enclosure kit H10 enclosure option kits** Model(s) 132B0221

**AC motor controllers, Type 1/IP21 top enclosure kit H6 enclosure option kits** Model(s) 132B0217

**AC motor controllers, Type 1/IP21 top enclosure kit H7 enclosure option kits** Model(s) 132B0218

**AC motor controllers, Type 1/IP21 top enclosure kit H8 enclosure option kits** Model(s) 132B0219

**AC motor controllers, Type 1/IP21 top enclosure kit H9 enclosure option kits** Model(s) 132B0220

**AC motor controllers, Type 1/IP21/IP4X top enclosure kit A1 enclosures, "FC302"** Model(s) 130B1121

**AC motor controllers, Type 1/IP21/IP4X top enclosure kit A2 enclosures, "FC302"** Model(s) 130B1122

**AC motor controllers, Type 1/IP21/IP4X top enclosure kit A3 enclosures, "FC302"** Model(s) 130B1123

**Accessory Enclosed** Model(s) 132B9110

**Accessory Open type Control Cards** Model(s) 134B1730, 134B1724, 134B1732, 134B1728, 134B1729, 134B1731, 134B1727, 134B1726

**Decoupling kit H10 11kW/15kW** Model(s) 132B0211

**Decoupling kit H6 30kW/37-45kW** Model(s) 132B0207/132B0242

**Decoupling kit H7 55kW/75kW** Model(s) 132B0208/132B0243

**Decoupling kit H8 90kW** Model(s) 132B0209

**Decoupling kit H9 2.2kW-7.5kW** Model(s) 132B0230

**Enclosed, AC Drive** Model(s) FCD315PT4P66EXR1D0F12T12C0, TR-150, TRV200

**Field installable options, Cascade controllers** Model(s) 175Z3100, 175Z3692, 175Z4455

**Field installable options, Fieldbus** Model(s) 175Z4362, 195N2100

**Field installable options, MCB112 PTC Relay card option B (60mA/20-28Vdc)** Model(s) 130B1137

**Field installable options, Memory extension cards** Model(s) 175Z0403, 175Z0904, 175Z1147, 175Z2906, 175Z3687, 175Z3688, 175Z7801

**Field installable options, Positionings and controllers** Model(s) 175Z3055, 175Z3057, 175Z4458, 175Z4459

**Field installable options, Profibus** Model(s) 175L 3669, 175Z0402, 175Z0404, 175Z2625, 175Z2905, 175Z3685, 175Z3686, 175Z3722, 175Z3723, 175Z4207, 175Z4208, 175Z4363, 175Z7800

**Field installable options, Relay cards (4 relay)** Model(s) 175Z1227, 175Z2500, 175Z2901, 175Z2902, 175Z3690, 175Z3691, 175Z3754, 175Z3755, 175Z4453, 175Z4454, 175Z7803

**Field installable options, Synchronization and positionings** Model(s) 175Z3053, 175Z3056, 175Z4456, 175Z4457

**Field installable options, Type 1 kits** Model(s) 175Z4620, 175Z4621

**Field installable options, Winders and reelers** Model(s) 175Z3245

**LCP H6, H7, H8, H9, H10** Model(s) 132B0200

**LCP panel mounting kit** Model(s) 132B0201

**LCP process kits** Model(s) 175Z0131, 175Z0401, 175Z7804, HVAC kit

**Motor coil options** Model(s) 195N3110

**Open or enclosed AC motor controllers** Model(s) VLT-2880, VLT-2881, VLT-2882

**Open type input harmonics filters for motor drives** Model(s) 130B1482, 130B1752, 130B1483, 130B1753, 130B1484, 130B1754, 130B1485, 130B1755, 130B1486, 130B1756, 130B1487, 130B1757, 130B1488, 130B1758, 130B1491, 130B1759, 130B1492, 130B1760, 130B1493, 130B1761, 130B1494

130B1762, 130B1495, 130B1763, 130B1496, 130B1764, 130B1497, 130B1765, 130B1498, 130B1766, 130B1499, 130B1768, 130B3165, 130B3167, 130B1751, 130B1769, 130B5212, 130B5246, 130B5213

130B5247, 130B5214, 130B5248, 130B5215, 130B5249, 130B5216, 130B5250, 130B5217, 130B5251, 130B5218, 130B5252, 130B5219, 130B5253, 130B5220, 130B5254, 130B5221, 130B5255, 130B5222, 130B5256, 130B5223, 130B5257, 130B5224, 130B5258, 130B5225, 130B5259, 130B5226, 130B5260, 130B5227, 130B5228

**Panel through mounting frame Type 12/3R A5 enclosures** Model(s) 130B1028

**Panel through mounting frame Type 12/3R B1 enclosures** Model(s) 130B1046

**Panel through mounting frame Type 12/3R B2 enclosures** Model(s) 130B1047

**Panel through mounting frame Type 12/3R C1 enclosures** Model(s) 130B1048

**Panel through mounting frame Type 12/3R C2 enclosures** Model(s) 130B1049

**RFI filters** Model(s) 195N3103

**RFI/LC filters** Model(s) 195L3100, 195L3101, 195N3100, 195N3101

**Trane drives** Model(s) TR1 2811

\* - May be marked differently than table, but within the ratings range indicated

+ - May be prefixed by alternate alphanumeric code.

@ - Limited voltage/current device, construction not specified.

Last Updated on 2017-10-23

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2017 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2017 UL LLC".