

Check Valves Catalog

In-line, Female Port


RS 13

OPERATION

This valve allows free flow from 1 to 2 and blocks flow from 2 to 1.

SPECIFICATIONS

Theoretical performance



Schematic




Specifications

Rated pressure	315 bar [4500 psi]
Rated flow at 7 bar 100 psi	100 l/min [26 US gal/min]
Weight	0.21 kg [0.46 lb]
Cavity	none

DIMENSIONS

mm in

Cross-sectional view



ORDERING INFORMATION

RS 13 / 0.5 - G

Ports

G = ½ BSP

Crack Pressure

0.5 = 0.5 bar [7 psi]

5 = 5 bar [73 psi]