



additional informations:
 filter colour : zink plated steel
 filter weight : 5,8kg



2pcs earth screws M6x16
 (with lockwasher and washer)


Label:

VLT MCC 102 du/dt FILTER Danfoss A/S 6430 Nordborg, Denmark
 www.danfoss.com

T/C: MCC102A40K1WE00B SN: 000169-316
 P/N: 130B2835 50/60/45 (max) 10/75
 3x 44A 600V / 3x 44A 600V / 3x 44A 600V SN: 4@800V 27A@800V
 Chassis/FP0 Term: 45°C/113°F

130B2835000169-316

Use only with a type 1 or type 2 SPD overvoltage control device
 LISTED E 21922 B 1406032 FA-Nr.: 000000
 Int. Cont. Eq. 1-HD1 U-requirements See manual for U-requirements EN 61589 CE



e|20.07.16| Schr./Fie. | Typelabel updated, Danfoss Postaddress included
 d|18.02.15| Fie./Eilers | new type
 | date | name | amendment





Dimensions toleranced according to ISO 2768-m						
Tolerance class	from 0,5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8

drawn	24.11.14	Eilers	Eilers	scale	1:4
checked	24.11.14	Flemming	Flemming	format	A4
date		name	signature		

Dimensions B 1406032
 du/dt filter 40A – IP00

order number	130B2835	dIN ISO 5456	drawing number	Z791411006	modi.	e	sheet	1/2
Please observe protection clause to ISO 16016								

included accessories
(screen connection plate)



Dimensions toleranced according to ISO 2768-m						
Tolerance class	0,5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8

drawn	24.11.14	Eilers	Eilers	scale	1:4
checked	24.11.14	Flemming	Flemming	format	A4
	date	name	signature		



Dimensions B 1406032		order number	130B2835	drawing number	Z791411006	modi.	e	sheet	2/2
du/dt filter 40A – IP00		Please observe protection clause to ISO 16016							

