

additional informations:
 filter colour : RAL 7001
 filter weight : 22,8kg
 accessories : 2x 195N3206
 screws : 4x M5x16mm DIN7985
 enclosure cover : with nylon lock washer
 label:



VL T MCC 102 du/dt FILTER Dannebrog Allé, 8430 Søborg, Danmark
 WWW.DANFOSS.COM

Tel: +45 70 02 40 00 Fax: +45 70 02 40 01
 E-mail: vl@danfoss.com

Part No: 130B2837
 Part No: 130B2837
 Part No: 130B2837
 Part No: 130B2837

MADE IN GERMANY
 L1: 1041
 C1: 1344
 P1: 1134V
 Weight: 22,8kg
 Volume: 20,4 dm³

B 1003006 F.A.N.C. 000020 EN 61558



- d | 28.04.16 | Schr./Fie. | typeable updated, Danfoss Postadress included, Core changed
- c | 19.11.14 | Schr./Fie. | typeable updated
- b | 30.09.10 | KOR/BRE | approval added
- a | 12.05.10 | KOR/BRE | additional informations added

Dimensions toleranced according to ISO 2768-m					
Tolerance class	from 0,5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5

drawn	16.04.10	Kornau	Kornau	scale	1:5
checked	16.04.10	Bremer	Bremer	format	A4
date			signature	DIN ISO 5456	
					order number
					130B2837
				all dimensions mm	drawing number
					Z791004021
					modi.
					d
					sheet
					1/1

Dimensions B 1003006
 du/dt filter 40A - IP54

Please observe protection clause to ISO 16016