



additional informations:

filter colour : RAL 7001  
 filter weight : 39,8kg  
 accessories : 2x 130B4045

**Label:**

<b>VLT</b> MCC 102 duft FILTER www.danfoss.com		Danfoss AG, 8130 Kadenze, Denmark Made in Germany	
TFC: MCC102AKMTKFE48 SN: 00016B-181 P/N: 130B2840 L-561H 3x 240x96V-100/0Hz (max. 100Hz) 3x 240x440V 60k@50V 62k@60V 54k@90V 3x 240x440V 60k@50V 62k@60V 54k@90V Net wt: 39,8kg Gross wt: 42,4kg Dimensions: 402x400x160mm Tightening torque: 2,2-2,4 Nm Filter class: G4		EN 61518 CE	

d| 3.05.16 Schr./File. typeable updated, Donfoss Postaddress included

c| 19.11.14 Schr./File. typeable updated

b| 02.07.10 KOR/BRE approval added

a| 11.05.10 KOR/BRE additional informations added  
 date name amendment

Dimensions toleranced according to ISO 2768-m			
Tolerance class	0,5	from 3	from 6
	3	to 6	to 30
m (middle)	±0,1	±0,1	±0,2
			±0,3
			±0,5
			±0,8

drawn	16.04.10	Kornau	Kornau	scale	1:6
checked	16.04.10	Bremer	Bremer	format	A4
	date	name	signature		

order number	130B2840	drawing number	Z791004022	mod.	d	sheet	1/1
--------------	----------	----------------	------------	------	---	-------	-----

Dimensions B 1003007  
 du/dt filter 80A – IP54  
 Please observe protection clause to ISO 16016

