




additional informations:
 filter colour : zink plated steel
 filter weight : 22kg



2pcs earth screws M6x16
 (with lockwasher and washer)



label:


VLT MCC 102 du/dt FILTER
 Danfoss A/S, 6430 Nordborg, Denmark
 www.danfoss.com

Part: MCC102A 1051 INE008 S/N: 001168-206
 P/N: 130B2841-9090CH (inner: 00-CH)
 3x 20A@90V - 9090CH (inner: 00-CH)
 3x 100A@940V - 055A@900V / 100A@900V 85A@930V
 C=150F
 Fuse: 3A-HF
 Weight: 22.0kg
 Terminal: 2x45.0mm
 only CU

130B28411000168-206

LISTED E119322 E0303112 F A NF 000000
 Use only with a type 1 or type 2 SF-D overvoltage control device

UL LISTED
 VDE
 CE







Dimensions B 0908112
 du/dt filter 105A - IP00

d	17.05.16	Schr./Fie.	typeable updated, Danfoss Postaddress included			
c	14.01.13	Schr./Kor.	typeable updated, accessories added			
b	02.07.10	KOR/BRE	approval added			
a	12.01.10	KOR/BRE	part-no. added			
	date	name	amendment			
Dimensions toleranced according to ISO 2768-m						
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8

drawn	18.11.09	Kornau	Kornau	scale	1:4
checked	18.11.09	Bremer	Bremer	format	A4
	date	name	signature		

order number	130B2841	drawing number	Z790911014	modi.	d	sheet	1/2
Please observe protection clause to ISO 16016							



included accessories
(screen connection plate)

d 17.05.16	Schr./Fe.	typelable updated, Dantoss Postaddress included
c 14.01.13	Schr./Kor.	typelable updated, accessories added
b 02.07.10	KOR/BRE	approval added
a 12.01.10	KOR/BRE	part-no. added
date	name	amendment

Dimensions toleranced according to ISO 2768-m						
Tolerance class	0,5	from 3	from 6	from 30	from 120	from 400
	to 3	to 6	to 30	to 120	to 400	to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8

drawn	18.11.09	Kornau	Kornau	scale	1:4
checked	18.11.09	Bremer	Bremer	format	A4
date		name	signature		



dll dimensions mm

Dimensions B 0908112
du/dt filter 105A – IP00

order number	130B2841	drawing number	Z790911014	modi.	d	sheet	2/2
Please observe protection clause to ISO 16016							