





additional informations:
 filter colour : impregnated
 filter weight : 33kg



Label:

VLT MCC 102 du/dt FILTER
 www.danfos.com

T/C: MCC102A3031W009 S/N: 001188-205
 P/N: 130B2847 5700H/70000
 3x 315A@40V 303A@500V 2A2A@300V 192A@900V
 Class:IP00 Temp: 45°C/113°F Weight: 33kg

130B2847/001188-205
 Use only with a type 1 or type 2 SPD overvoltage control device

LISTED E215022 B 00061-4 FA-Nr.: 000000
 1rd Cont. Eip. See manual for UL-requirements

MADE IN GERMANY
 L5501PE
 IP00-3Hz
 P/req: 315kW
 Tripping torque
 10Nm

EN 61588 **CE**

d18.05.16	Schr./File.	Postaddress updated
c25.03.13	Schr./Kor.	typelabel updated
b102.07.10	KOR/BRE	approval added
a13.01.10	KOR/BRE	part-no. added
date	name	amendment

Dimensions toleranced according to ISO 2768-m						
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8

drawn	18.11.09	Kornau	Kornau	scale	1:4,5
checked	18.11.09	Bremer	Bremer	format	A4
date		name	signature	DIN ISO 5456	

order number	130B2847	dll dimensions mm
drawing number	Z790911018	

Dimensions B 0908114
 du/dt filter 303A – IP00

Please observe protection clause to ISO 16016

modi.	d	sheet	1/1
-------	---	-------	-----