

additional informations:  
 filter colour : RAL7001  
 filter weight : 64,5kg

label:

**VLT** MCC 102 du/dt FILTER  
 www.dantoss.com




Dantoss A/S, 6430 Nordang, Denmark  
 MADE IN GERMANY

TTC: MCC102A3031TWZ238 S.N.: 000170-206  
 P.N.: 130B2948 C=20UH  
 3x 380-680V - 50/60Hz (max.100Hz) ISW=3kHz  
 3x 315@440V 303A@500V 2x2A@600V 192A@900V  
 NEMA 1/1P23 Tamb. 45°C/113°F F=315VW  
 \*30B234600170-205\*

Use only with a type 1 or type 2 SEP, overvoltage control device.

EN 61558

CE



f 19.05.16	Schr./Fle.	typelabel updated, Dantoss Postaddress included
e 26.11.14	Schr./Kor.	typelabel updated
d 10.04.13	Schr./Kor.	typelabel updated
c 25.03.13	Schr./Kor.	typelabel updated
b 02.07.10	KOR/BRE	approval added
a 12.01.10	KOR/BRE	part-no. added
date	name	amendment

Dimensions toleranced according to ISO 2768-m						
Tolerance class	0,5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0,1	±0,1	±0,2	±0,3	±0,5	±0,8

drawn	18.11.09	Kornau	Kornau	scale	1:5
checked	18.11.09	Bremer	Bremer	format	A4
date		name	signature		

Dimensions B 0908114.2  
 du/dt filter 303A – 1P23

order number	130B2848	drawing number	Z790911019	modi.	f	sheet	1/1
Please observe protection clause to ISO 16016							

