






additional informations:
 filter colour : impregnated
 filter weight : 265kg

label:

VLT MCC 101 sine wave FILTER
 www.dantloss.com
 Danloss A/S 8460 Nordborg, Denmark
 T/C: MCC101A5107E00B S/N: 000168-176
 P.N.: 130B3188
 3x 510A/510A-463A/510A-283A @ 100Hz
 Chassis/PO: Tamb. 45°C/113°F
 Weight: 265kg
 Tightening torque terminal: 50Nm
 *130B3188000168-176
 Use only with a type 1 or type 2 SPD overvoltage control device
 E 210022 EN 61508 F44V: 000000
 EN 61508 EN 61508 CE



Detail A:
 scale 3:1

d 28.04.16	Schr./File.	Dantloss updated	typelabel updated
c 22.12.14	Schr./File.	Postadress included	typelabel updated
b 11.03.13	Schr./Kor.	ccp. connectors changed to bolt	typelabel updated
a 30.09.10	KOR/ Lau	approval added	typelabel updated
date	name	approval added	amendment

Dimensions toleranced according to ISO 2768-m			
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30
m (middle)	± 0.1	± 0.1	± 0.2
		from 30 to 120	from 120 to 400
			from 400 to 1000
			± 0.8

drawn	01.06.10	Kornrau	Kornrau	scale	/
checked	01.06.10	Bremer	Bremer	formate	A4
	date	name	signature		

Dimensions B 1001076
 sine-wave filter 500V 510A - IP00

order number	130B3188	drawing number	Z791004006	modi.	d	sheet	1/1
--------------	----------	----------------	------------	-------	---	-------	-----

Please observe protection clause to ISO 16016

1 2 3 4 5 6 7 8