

additional informations:
 filter colour : impregnated
 filter weight : 410kg

VLT[®] MCC 101 sine wave FILTER
 www.gantoss.com




T/C: MCC101A66073E08 S/N: 000106-106
 P.N: 130B3191 3x 280-300V / 500Hz (max. 100Hz)
 3x 280-300V / 500Hz (max. 100Hz)
 Careship00 7 arm: 45°C/1.3°
 4113531310003681581

MADE IN GERMANY
 L=150µH
 Cr=318pF
 Pass: 2000W
 Weight: 410kg
 Tightening torque
 Terminal: 50Nm

Use only with 2 SPD surgeprotector control device.

E10101077 EAN: 000307
 EN 61556

Industria, 1101



e 02.05.16	Schr./Fie.	typelabel updated				
d 22.12.14	Schr./Fie.	Dantoss Postaddress included				
c 14.07.14	Schr./Fie.	typelabel updated				
b 11.03.13	Schr./kor.	cap. connectors changed to bolt numbers of capacitors corrected				
a 30.09.10	KOR/Lauer	typelabel updated				
date		approval added				
name		amendment				
Dimensions toleranced according to ISO 2768-m						
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8

drawn	01.06.10	Kornrau	Kornrau	scale /
checked	01.06.10	Bremer	Bremer	formate A4
date		name		signature

Dimensions B 1001077
 sine-wave filter 500V 660A – IP00

order number 130B3191 drawing number Z791004007

mod. e sheet 1/1

Please observe protection clause to ISO 16016