

additional informations:
 filter colour : zink plated steel
 filter weight : 18kg

label:





VLT MCC 101 sine wave FILTER
 www.danfoss.com Danfoss A/S 8490 Nordborg Denmark

T/C: MCC101A13K7TE08B S/N: 000169-186
 P.N.: 130B3195
 3x3x2-90V - 50/60Hz (max. 00Hz)
 Filtered frequency: 50/60Hz
 Chassis/imp0 Term: 45°C/13.7°C
 +130B3195/000169-186

MADE IN GERMANY
 L-4g 17H
 C-4g 17F
 Pos: 115V/
 Weight: 18kg
 Tightening torque terminal 2x4: 0.8Nm
 5703 22

Use only with a type 1 or type 2 SPD overvoltage control device

E 10027946 EAXX 000300
 E 10027946 EAXX 000300
 EN61558 EN61558



e 04.05.16	Schr./Fie.	typelable updated, Danfoss Postaddress included
d 10.11.14	Schr./Fie.	typelable updated
c 13.08.13	KOR/Fie.	cabling updated
b 14.01.13	Schr./KOR	typelable updated, accessories added
a 01.10.10	KOR/Lauer	approval added
	date	amendment

Dimensions toleranced according to ISO 2768-m						
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8
m (middle)						


drawn	04.06.10	Kornrau	Kornrau	scale	1:4
checked	04.06.10	Bremer	Bremer	format	A4
	date	name	signature		

Dimensions B 1002049
 sine wave filter 690V 13A - IP00




order number 130B3195
 drawing number Z791004009
 mod.: e
 sheet 1/2

Please observe protection clause to ISO 16016

1 2 3 4 5 6 7 8



included accessories
(screen connection plate)



e 04.05.16	Schr./Fie.	typelable updated, Danfoss Postaddress included
d 10.11.14	Schr./Fie.	typelable updated
c 13.08.13	KOR/Fie.	cabling updated
b 14.01.13	Schr./KOR	typelable updated, accessories added
a 01.10.10	KOR/Lauer	approval added
date	name	amendment

Dimensions toleranced according to ISO 2768-m						
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8

drawn	04.06.10	Kornrau	Kornrau	scale	1:4
checked	04.06.10	Bremer	Bremer	format	A4
date		name	signature		

Dimensions B 1002049
sine wave filter 690V 13A - IP00

order number	130B3195	drawing number	Z791004009	modi.	e	sheet	2/2
--------------	----------	----------------	------------	-------	---	-------	-----

dll dimensions mm

Please observe protection clause to ISO 16016