

additional informations:
 filter colour : zinc plated steel
 filter weight : 43kg

label:

VLT MCC-101 sine wave FILTER
 www.danloss.com

T/C: MCC-101/4K/NT/2018
 P/N: 130B4114
 3K: 42A/60Hz 42A/60Hz 33A/0/0Hz
 Chassis: 400 1 amp 45°C/113°

SIN 0001691188
 MADE IN GERMANY
 L=220mm
 H=100mm
 W=450mm
 Weight: 43kg





130B4114/0001150 188x
 130B4114/0001150 188x

Use only with a type 1 or type 2 SPD overvoltage protection device

E 270622 - H01
 EN 61025
 EN 61058

UL 94V-0
 UL-Requirement

F 4127 000000
 E 4127 000000
 EN 61058



- e|04.05.16| Schr./Fie. | typeable updated, Danfoss Postaddress included
 - d|10.11.14| Schr./Fie. | typeable updated
 - c|13.08.13| KOR/Fie. | cabling updated
 - b|14.01.13| Schr./KOR | typeable updated, accessories added
 - a|01.10.10| KOR/Lauer | approval added
- | date | name | amendment |
|------|------|-----------|
| | | |

Dimensions toleranced according to ISO 2768-m					
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400
	±0.1	±0.1	±0.2	±0.3	±0.5
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.8

drawn	checked	date	name	signature	formate	scale
04.06.10	04.06.10	04.06.10	Kornrau	Bremer	A4	1:4

Dimensions B 1002051

sine wave filter 690V 45A - IP00

order number 130B4114

drawing number Z791004011

Please observe protection clause to ISO 16016

additional informations:
 filter colour : zinc plated steel
 filter weight : 43kg

label:

VLT MCC-101 sine wave FILTER
 www.danloss.com

T/C: MCC-101/4K/NT/2018
 P/N: 130B4114
 3K: 42A/60Hz 42A/60Hz 33A/0/0Hz
 Chassis: 400 1 amp 45°C/113°





SIN 0001691188
 MADE IN GERMANY
 L=220mm
 H=100mm
 W=450mm
 Weight: 43kg

130B4114/0001150 188x
 130B4114/0001150 188x

Use only with a level 1 or higher 2 SPD overvoltage protection device

E 270622 - H01 - E 1420251 - E 1420250
 Indicated by - H01 - E 1420251 - E 1420250
 UL94 V0 - UL94 V0
 UL94 V0 - UL94 V0

EN 61258 CE



- e|04.05.16| Schr./Fie. | typeable updated, Danfoss Postaddress included
 - d|10.11.14| Schr./Fie. | typeable updated
 - c|13.08.13| KOR/Fie. | cabling updated
 - b|14.01.13| Schr./KOR | typeable updated, accessories added
 - a|01.10.10| KOR/Lauer | approval added
- | date | name | amendment |
|------|------|-----------|
| | | |

Dimensions toleranced according to ISO 2768-m					
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400
	±0.1	±0.1	±0.2	±0.3	±0.5
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.8

drawn	04.06.10	Kornrau	Kornrau	scale	1:4
checked	04.06.10	Bremer	Bremer	format	A4
date			signature		

Dimensions B 1002051
 sine wave filter 690V 45A - IP00

order number	130B4114	drawing number	Z791004011	modi.	e	sheet	1/2
Please observe protection clause to ISO 16016							

1 2 3 4 5 6 7 8

F E D C B A

F E D C B A