



additional informations:
 filter colour : RAL 7001
 filter weight : 14,5kg
 accessories : 2x 195N3206
 : 4x M5x16mm DIN7985
 enclosure cover with nylon lock washer

VLIT MOC 101 sine wave FILTER
 www.danfoss.com

Denfoss A/S 8500 Vejdskov, Denmark
 MADE IN GERMANY
 L: 6,31µm
 C: 3,3µm
 S: 2,2µm
 P: 1,1µm
 Weight: 14,5kg
 Terminal: 0,5" - 0,75"

PN: 13462835
 3x 52x480V - 50/60Hz (max.100Hz)
 3x 4,5A@50Hz - 4,0A@60Hz - 3,0A@100Hz
 1.3462835000103-460

B: 1352022 FA: NR: 000003 EN 61855 **CE**



a|30.11.16| Schr./Fla. | Change index to "a"
 date | name | amendment

Dimensions	toleranced	according to	ISO 2768-m
Tolerance class	0,5 to 3	from 3 to 6	from 30 to 120
m (middle)	±0,1	±0,1	±0,2
			from 120 to 400
			from 400 to 1000
			±0,5
			±0,8

drawn	24.11.16	Schröder	Schröder	scale	1:5
checked	24.11.16	Flemming	Flemming	format	A4
date		name	signature	DIN ISO 5456	

Dimensions B 1605022

sine wave filter 690V 4,5A - IP54

order number	134B2835	drawing number	Z791609002	modi.	Q	sheet	1/1
--------------	----------	----------------	------------	-------	---	-------	-----

Please observe protection clause to ISO 16016

