



additional informations:

filter colour : RAL 7001
 filter weight : 36,6kg
 accessories : 2x 195N3206

VLT® MCC 101 sine wave FILTER
 www.danfoss.com

MADE IN GERMANY
 C=100UF
 R=0,4kΩ
 P=0,18W
 T=100°C
 Terminal 2, 0,4 3pin

TC: MCC 01A2K7E5B8 SN: 207163-488
 3x 635-680V / 50/60Hz max.100Hz
 3x 27,0A@90Hz / 20,0A@96Hz / 14,0A@100Hz
 NEMA 27F54 Term. 45°C/113°F
 13482837000155-463

B 1605112 FAAN:CO0002 EN 61558



d 30.11.16 | Schr./File: | Change index to "a"
 date | name | amendment

Dimensions toleranced according to ISO 2768-m

Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0,1	±0,1	±0,2	±0,3	±0,5	±0,8

drawn	24.11.16	Schröder	Schröder	scale	1:6
checked	24.11.16	Flemming	Flemming	format	A4
date		name	signature	DIN ISO 5456	

Dimensions B 1605112
 sine wave filter 690V 22A – IP54

order number	134B2837	drawing number	Z791610003	modi.	Q	sheet	1/1
Please observe protection clause to ISO 16016							