





output terminals
 U2, V2, W2: 120mm²
 Tightening torque: 12.0-20.0Nm

input terminals
 U1, V1, W1, R+: 50mm²
 Tightening torque: 3.5-6.0Nm




A (1 : 3.5)



Cable clamp PUK 28B
 Danfoss part-No. 175Z1707

Cable clamp PUK 60B



- included accessories**
- 1x decoupling plate
 - 1x cable clamp PUK 28B
 - 1x cable clamp PUK 60B
 - 2x cable clamps R=35
 - 4x screws M4x25
 - 2x combi-screws M6x16
 - 4x screws M6x12

Surface filter color RAL 7001				Weight 69.7kg		MCC201A62KT3E20B			
C	30.10.2020	Besbes	312255	Scale 1:8	All Mode Sine-Wave Filter 65A 400V IP20				
B	06.10.2020	Besbes	306590						
Rev	Datam	Name	Modification						
Cons.	30.10.2020	Besbes	General tolerance	Order number 175U6065		Drawing Number-Revision-Version 223277-C-0			
Draw.	30.10.2020	Besbes	ISO 2768-mK						
Check.	30.10.2020	Eilers	ISO 5456 						
Observe protection clause to ISO 16016						Sheetsize A4		Sheet 1/1	