





Type	Value
Max Weight	65 kg / 143 lb
IP Class	IP21
Nema Class	Type 1







DETAIL C  
SCALE 1:2



DETAIL B  
SCALE 1:1




DETAIL A  
SCALE 1:1



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.  
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

**● CENTER OF GRAVITY:**  
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS $\pm 1$ MM (0,4 INCH). ALL DIMENSIONS ARE IN MILLIMETERS (INCH)			FIRST ANGLE PROJECTION	SCALE	SIZE	MATERIAL	
				1:10	A3		
					FINISH		
					DESCRIPTION		
					MCAD FC C2 IP21 WITH DISCONNECT		
CHANGED							
DESIGNED	Danfoss	2015-04-23					
CHECKED							
PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.						DRAWING NUMBER	REV
						MCAD-FC-C2-IP21-WITH-DISCONNECT	P1
						MODEL	SHEET
						C2-CUSTOMER-DRAWING	1 OF 2



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.  
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL  
REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.

DRAWING NUMBER	REV
MCAD-FC-C2-IP21-WITH-DISCONNECT	P1
MODEL	SHEET
C2-CUSTOMER-DRAWING	2 OF 2