



- (17) General bending radius: 1 mm
- (18) Corner rounds not specified: $R2.5 \pm 0.5$
- (19) Part must be washed and degreased
- (20) Material specification:
1.0mm Sheet acc. to EN 10346-DX51D+AZ150-N-A-C
- (21) Not specified dimensions according to unfolded part

Projection 	Scale / Paper size 1:2 / A3	 DANFOSS DRIVES A/S	Matr./Spec. See note
Last revised by H. Jessen			Date 2013.05.21
Confidential: Property of Danfoss Drives A/S. Not to be handed over to, copied or used by third party. Two- or three dimensional reproduction of contents to be authorized by Danfoss Drives A/S.			Designation Backplate C4
PDM controlled drawing. - Hard copy not valid without frozen date in ID stamp.			Part no. 130B4229
			Sh. 1 of 2
			Rev. 002

Model: 130B4229.PART



24
For internal use: Y bending factor = 0.58

		Scale / Paper size 1:1 / A2		Metr. /Spec. Danfoss standard
Last revised by H. Jessen	Date 2013.05.21	DANFOSS DRIVES A/S		Designation Backplate C4, unfolded
Confidential: Property of Danfoss Drives A/S. Not to be handed over to, copied or used by third party. Two- or three dimensional reproduction of contents to be authorized by Danfoss Drives A/S.			Part no 130B4229	Sh. 2 of 2
PDM controlled drawing. - Hard copy not valid without frozen date in ID stamp.			Rev. 002	

Model: 130B4229.PART