



Type	Value
Max Weight	55.6 Kg
IP Class	IP 00
UL Type	Open
Frame Size	S1C06





DETAIL A (1 : 1)



DETAIL B (1 : 1)




DETAIL C (1 : 1)



tolerances according to ISO 2768-mK

class	0.5mm - 3mm	>3mm - 6mm	>6mm - 30mm	>30mm - 120mm	>120mm - 400mm	>400mm - 1000m
m	+/- 0.1mm	+/- 0.1mm	+/- 0.2mm	+/- 0.3mm	+/- 0.5mm	+/- 0.8mm
class	up to 10mm	>10mm - 30mm	>30mm - 100mm	>100mm - 300mm	>300mm - 1000mm	>1000mm - 3000mm
K	0.05mm	0.1mm	0.2mm	0.4mm	0.6mm	0.8mm

ALL DIMENSIONS ARE IN MILLIMETERS [INCH]		FIRST ANGLE PROJECTION	SCALE 1:5	DRAWING SIZE A3	MATERIAL	
					FINISH	
					DESCRIPTION	
CHANGED					Sine-wave Filter 73.0A IP00	
DESIGNED					OF7S1-S-AN-25-73A0-070-TX-E00	
CHECKED					132H5067	
PROPERTY OF DANFOSS A/S NORDBORG, DENMARK, TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.					MODEL: 132H5067	
					REV 004	
					SHEET 1 OF 4	



Included accessories

Pos.	Pcs.	Description	Type
1	1	Decoupling plate	
2	4	Combi screws	M6 x 20 T30
3	2	Cable clamp	
4	2	Eye bolt for lifting	M8
5	2 / 2	Cable clamp	PUK 36B / 40B

+ Premounted


Pos.	Pcs.	Description	Type
6	4	Combi screws	M6 x 16 T30
7	4	Combi screws	M4 x 12 T20

For installation environments described by IEC 60721-3-3 3M11 use 4 screws (A)


For installation environments described by IEC 60721-3-3 3M12 use 8 screws (A&B)

ALL DIMENSIONS ARE IN MILLIMETERS [INCH]		FIRST ANGLE PROJECTION	SCALE	DRAWING SIZE	MATERIAL
			1:5	A3	
					FINISH
					DESCRIPTION
					Sine-wave Filter 73.0A IP00 OF7S1-S-AN-25-73A0-070-TX-E00 132H5067
					MODEL: 132H5067
CHANGED					REV 004
DESIGNED					SHEET 2 OF 4
CHECKED					
PROPERTY OF DANFOSS A/S NORDBOURG, DENMARK, TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.					


Mounting conditions




Label location



DETAIL E (3 : 5)





DETAIL F (3 : 5)



tolerances according to ISO 2768-mK						
class	0.5mm - 3mm	>3mm - 6mm	>6mm - 30mm	>30mm - 120mm	>120mm - 400mm	>400mm - 1000m
m	+/- 0.1mm	+/- 0.1mm	+/-0.2mm	+/-0.3mm	+/-0.5mm	+/- 0.8mm
class	up to 10mm	>10mm - 30mm	>30mm - 100mm	>100mm - 300mm	>300mm - 1000mm	>1000mm - 3000mm
K	0.05mm	0.1mm	0.2mm	0.4mm	0.6mm	0.8mm

ALL DIMENSIONS ARE IN MILLIMETERS [INCH]		FIRST ANGLE PROJECTION	SCALE	DRAWING SIZE	MATERIAL
			1:5	A3	
		FINISH			
		DESCRIPTION			
		Sine-wave Filter 73.0A IP00			
		OF7S1-S-AN-25-73A0-070-TX-E00			
		132H5067			
CHANGED					REV 004
DESIGNED					SHEET 3 OF 4
CHECKED					
PROPERTY OF DANFOSS A/S NORDBOURG, DENMARK, TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.					MODEL: 132H5067

Product label (58x30mm)

Sine-wave FILTER OF7S1
 T/C: OF7S1-S-AN-25-73A0-070-TX-E00
 P/N: 132H5067 S/N: DMZZZ65 - 2224 / DM
 200-240V, 74.8A@70Hz, 63.6A@100Hz, 63.6A@120Hz
 380-440V, 73.0A@70Hz, 62.1A@100Hz, 62.1A@120Hz
 441-500V, 66.0A@70Hz, 56.1A@100Hz, 56.1A@120Hz
 Tamb: -30°C/-22°F - 45°C/113°F
 ENCL: IP00 / Open type
 IND.CONT.EQ. 1HD1
 ta(max)=45°C
LISTED E 223655
 B 1710084
 L: 0.74mH, Cy: 90.0µF
 fsw: ≥ 2kHz
 Ploss: ≤ 398W
 Weight: 55.6kg
 Terminal torque: 14Nm
 Frame: S1C06
 DK-6430 Nordborg
 www.danfoss.com
 MADE IN GERMANY
 FA-Nr.: 000000

Product label (58x18mm)

 EN61558
 Danfoss Ltd. 22 Wycombe End,
 HP9 1NB, GB
   ≤ 5000m 



Product label (30x16mm)


DANGER
 See manual/Voir manuel

Packaging label (100x59mm)

Sine-wave Filter OF7S1
 T/C: OF7S1-S-AN-25-73A0-070-TX-E00
P/N: 132H5067
 S/N: DMZZZ65 - 2245 / DM
 200-240V: 74.8A Tstorage: -30°C/-22°F - 70°C/158°F
 380-440V: 73.0A ENCL: IP00 / Open type
 441-500V: 66.0A Frame: S1C06
 Weight: 72.1kg
 **MADE IN GERMANY**
 5 714853 340828


 ZZZZ652245
 EN61558
 Danfoss Ltd. 22 Wycombe End,
 HP9 1NB, GB
 Danfoss A/S,
 DK-6430 Nordborg
 www.danfoss.com
 
 B 1710084 FA-Nr.: 000000

ALL DIMENSIONS ARE IN MILLIMETERS [INCH]		FIRST ANGLE PROJECTION 	SCALE 1.5:1	DRAWING SIZE A3	MATERIAL
CHANGED				FINISH	
DESIGNED				DESCRIPTION	
CHECKED				Sine-wave Filter 73.0A IP00 OF7S1-S-AN-25-73A0-070-TX-E00 132H5067	
PROPERTY OF DANFOSS A/S NORDBORG, DENMARK, TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.				MODEL: 132H5067	REV 004 SHEET 4 OF 4