




additional informations:

filter colour : zink plated steel
 filter weight : 12,7kg



2pcs earth screws M6x16
 (with lockwasher and washer)




Label:

VLT[®] MCC 102 du/dt FILTER
 www.danfoss.com

Danfoss A/S 8430 Nordborg, Denmark
 Tlf: +45 73 53 53 53 Fax: +45 73 53 53 53
 C-11111111 C-11111111
 33.50A@94A0V 80A@6300V 62A@800V 54A@960V
 Chassis:IP00 Term: 45°C/113°F
 130E2838000168-196
 Use only with a type 1 or type 2 SPD overvoltage control device
 LISTED E219022 B 0908111 FA-Nr.: 000000
 Ind.Co.Eng. 1HD1 See manual for UL-requirements
 EN 61558

MADE IN GERMANY
 C-11111111 C-11111111
 Pless: 120W Weight: 12,7kg
 Tightening torque terminal: 2,0-4,0Nm only CU



d 13.05.16	Schr./File.	typelable updated, Danfoss Postadress included
c 14.01.13	KOR./Kor.	typelable updated, accessories added
b 02.07.10	KOR/BRE	approval added
a 12.01.10	KOR/BRE	part-no. added
date	name	amendment

Dimensions toleranced according to ISO 2768-m						
Tolerance class	0,5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0,1	±0,1	±0,2	±0,3	±0,5	±0,8





drawn	18.11.09	Kornau	Kornau	scale	1:4
checked	18.11.09	Bremer	Bremer	format	A4
date				signature	



all dimensions mm

Dimensions B 0908111
 du/dt filter 80A – IP00

order number	130B2838	drawing number	Z790911012	modi.	d	sheet	1/2
Please observe protection clause to ISO 16016							



included accessories
(screen connection plate)

d|13.05.16 Schr./Fie. typeable updated, Danfoss Postaddress included
 c|14.01.13 Schr./Kor. typeable updated, accessories added
 b|02.07.10 KOR/BRE approval added
 a|12.01.10 KOR/BRE part-no. added
 date name amendment

Dimensions tolerated according to ISO 2768-m	
Tolerance class	0,5 to 3
m (middle)	$\pm 0,1$
	from 3 to 6
	from 6 to 30
	from 30 to 120
	from 120 to 400
	from 400 to 1000
	$\pm 0,1$
	$\pm 0,2$
	$\pm 0,3$
	$\pm 0,5$
	$\pm 0,8$

drawn	18.11.09	Kornau	Kornau	scale	1:4
checked	18.11.09	Bremer	Bremer	format	A4
	date	name	signature		



all dimensions mm

Dimensions B 0908111
du/dt filter 80A – IP00

order number	130B2838	drawing number	Z790911012	modi.	d	sheet	2/2
Please observe protection clause to ISO 16016							

