





additional informations:
 filter colour : impregnated
 filter weight : 47kg




PE bolt M8
 (2x washer, 1 lock washer, 1 nut)
 label:

VLT MCC 102 dust FILTER
 Carlsson A/S, Østergade, Denmark
 www.danfoss.com
 T/C: MCC102A6457ME008 S/N: 000186-208
 P/N: 130B2851
 3x 38x48x90V - 5000hPa (max. 100hPa) 52A@900V 450A@990V
 Class: 1000 1 amp 45°C@113°F
 4535253100C158 3206
 Use only with UL type listed components
 UL type listed components: 60000027 57A-UL: 000000
 not certified for UL requirements
 MADE IN GERMANY
 L=81H
 C=86H
 P=550W
 Weight: 47kg
 Tightening torque
 terminal: 50Nm
 EN 61558 CE



Detail A:
 scale 3:1



d19.05.16 | Schr./File: typeabel updated, Danfoss Postadress included
 c25.03.13 | Schr./Kor.: typeabel updated
 b12.07.10 | KOR/BRE: approval added
 a12.01.10 | KOR/BRE: part-no. added
 date name amendment

Dimensions toleranced according to ISO 2768-m						
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8

drawn	18.11.09	Kornau	Kornau	scale	1:4,5
checked	18.11.09	Bremer	Bremer	format	A4
date				DIN ISO	5456

Dimensions B 0909037
 du/dt filter 590A – IP00

order number	130B2851	drawing number	Z790911022	modi.	d	sheet	1/1
Please observe protection clause to ISO 16016							

F 1 2 3 4 5 6 7 8