

additional informations:  
 filter colour : RAL7001  
 filter weight : 78,5kg

label:

**VLT** MCC 102 du/dt FILTER  
 www.danfoss.com  
 Danfoss A/S 8450 Nordborg, Denmark

TIC: MCC10245457ME238  
 P/N: 130B2852  
 3x380-690V / -50/60Hz (max. 100Hz)  
 3x559A@440V / 590A@500V 523A@600V  
 NEMA 1/IP23 Tamb. 45°C/113°F

S/N: 000170-206  
 450A@660V





MADE IN GERMANY  
 L=150H  
 C=66H  
 fsw=2kHz  
 Ploss=550W  
 Weight: 78.5kg  
 Tightening torque terminal:30Nm

\*130B2852000170-206\*

Use only with a Type 1 or type 2 SPD overvoltage control device

E 21902Z  
 B 0909037.2 FA-N: 000000  
 See manual for CE requirements

EN 61538 **CE**



†19.05.16 | Schr./File. type/label updated, Danfoss Postaddress included  
 †17.04.15 | Schr./File. type/label updated  
 †10.04.13 | Schr./Kor. type/label updated  
 †05.03.13 | Schr./Kor. type/label updated  
 †02.07.10 | KOR/BRE approval added  
 †12.01.10 | KOR/BRE part-no. added  
 date name ornament

Dimensions toleranced according to ISO 2768-m

Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8
m (middle)						

drawn	18.11.09	Kornau	Kornau	scale	1:5
checked	18.11.09	Bremer	Bremer	format	A4
	date	name	signature		

DIN ISO 5456

all dimensions mm

Dimensions B 0909037.2  
 du/dt filter 590A – IP23

order number 130B2852  
 drawing number Z790911023

Please observe protection clause to ISO 16016

modi. f  
 sheet 1/1