



additional informations:  
 filter colour : impregnated  
 filter weight : 72kg



PE bolt M8  
 (2x washer, 1 lock washer, 1 nut)

**label:**

**VLT** MCC 102 duval FILTER

www.vltmess.com

MADE IN GERMANY

702: MCC 102/480T/MEN/03 S.N. 0010188-238

3x 380/480V - 50/60Hz (max. 100Hz)

3x 380V @ 440V 780A @ 50/60V 630A @ 690V

Classical IP00 Term. 4/5 211°/131°

+37928530001687-235



Use only with a type 1 or type 2 SPD overvoltage control device

EN 61558


UL requirements

EN 61558

CE



Detail A:  
 scale 3:1



d:19.05.16 | Schr./Fre. Typlabel updated, Dornros Postadress included  
 c:25.03.13 | Schr./Kor. Typlabel updated  
 b:30.09.10 | KOR/BRE approval added  
 a:13.01.10 | KOR/BRE part-no. added

date	name	amendment

Dimensions toleranced according to ISO 2768-m

Tolerance class	from 0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8

drawn	18.11.09	Kornau	Kornau	scale	1:5
checked	18.11.09	Bremer	Bremer	format	A4
date					

Dimensions B 0909038  
 du/dt filter 780A – IP00

DIN ISO 5456	order number	drawing number	modi.	sheet
	130B2853	Z790911024	d	1/1

Please observe protection clause to ISO 16016

