





additional informations:
 filter colour : impregnated
 filter weight : 197kg



Detail A:
 scale 3:1



VL T MCC 101 sine wave FILTER
 www.dantoss.com
 DanToss A/S, 8430 Nærbø, Denmark

T/C: MCC101A26073E00B S/N: 000168-178
 P/N: 130B3184
 3x 380-500V - 50/60Hz (max: 100Hz)
 3x 260A @50Hz - 260A @60Hz - 195 @100Hz
 Dimensions: frame: 453x113x137
 130B3184/00159-176

Use only with a type 1 or type 2 SPD overvoltage control device

LISTED ENEC 130B3184 B170072 P-KN: 000000
 130B3184 130B3184 130B3184
 CE

MADE IN GERMANY
 L=340UH
 C_Y=75µF
 P_{max}=3500W
 Weight: 197kg
 Tightening torque terminal: 18Nm

EN 61558

- e) 27.04.16 Schr./File. type label updated
- d) 22.12.14 Schr./File. DanToss Postaddress included
- c) 06.03.13 Schr./Kor. type label updated
- b) 30.09.10 KOR/Lau approval added
- a) 01.06.10 KOR/BRE new mechanical design

Dimensions tolerated according to ISO 2768-m					
Tolerance class	0,5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400
m (middle)	±0,1	±0,1	±0,2	±0,3	±0,5

drawn	12.04.10	Kornrau	Kornrau	scale	/
checked	12.04.10	Bremer	Bremer	format	A4
date		name	signature	DIN ISO 5456	

Dimensions B 1001074					
sine-wave filter 500V 260A - IP00					
order number	130B3184	drawing number	Z791004004	modi.	e
Please observe protection clause to ISO 16016					
					sheet 1/1