

additional informations:  
 filter colour : RAL7001  
 filter weight : 31kg  
 cable clamp : 2x 195N3206

**VLT** MCC 101 sine wave FILTER  
 www.danfloss.com Danfoss A/S, 6430 Nordborg, Denmark

T/C: MCC10128KTTZ0B S/N: 000168-186  
 P/N: 130B4113  
 3x 525-90V - 50/60Hz (max 100Hz)  
 3x 28A @ 90Hz - 28A @ 60Hz L/N @ 100Hz  
 0.85mS @ IP20 Term: 45°C @ 1.31\*



\*130B4113000168-186\*

Use only with a type 1 or type 2 SPD overvoltage control device

E 215022 Ind Coat Egn. HDI B 1002050 1 FA-Nr.: 000000  
 ULx=900V See manual for UL-requirements

MADE IN GERMANY  
 L=4.0mH  
 Is=10A  
 Ics=150V  
 Weight: 31kg  
 Tightening torque terminal: 2.0-4.0Nm  
 only CU

EN 61558 **CE**



d | 04.05.16 | Schr./Fie. | type/able updated, Danfoss Postaddress included

c | 10.11.14 | Schr./Fie. | type/able updated

b | 14.01.13 | Schr./Kor. | type/able updated

a | 01.10.10 | KOR/Lauer | approval added

Dimensions toleranced according to ISO 2768-m						
Tolerance class	from 0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8





drawn	04.06.10	Kornau	Kornau	scale	1:5
checked	04.06.10	Bremer	Bremer	format	A4
	date	name	signature		

Dimensions B 1002050.1  
 sine wave filter 690V 28A - IP20

order number	130B4113	drawing number	Z791004034	modi.	d	sheet	1/2
--------------	----------	----------------	------------	-------	---	-------	-----

DIN ISO 5456  
 all dimensions mm  
 Please observe protection clause to ISO 16016

included accessories  
(screen connection plate)



d 04.05.16	Schr./Fie.	typelible updated,	Danfoss Postaddress included
c 10.11.14	Schr./Fie.	typelible updated	
b 14.01.13	Schr./Kor.	typelible updated	
a 01.10.10	KOR/Lauer	approval added	
date	name	amendment	

Dimensions toleranced according to ISO 2768-m							
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000	
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8	

drawn	04.06.10	Kornau	Kornau	scale	1:5
checked	04.06.10	Bremer	Bremer	format	A4
date		name	signature		

Dimensions B 1002050.1  
sine wave filter 690V 28A – IP20

DIN ISO 5456	
all dimensions mm	

order number	130B4113	drawing number	Z791004034	modi.	d	sheet	2/2
Please observe protection clause to ISO 16016							