



input terminals
 U1, V1, W1, R+: 10mm²
 Tightening torque: 1.2-2.0Nm

output terminals
 U2, V2, W2: 16mm²
 Tightening torque: 2.0-4.0Nm



A (1 : 1.5)



Cable clamp R=25,6
 Danfoss Part-No. 195N3206

included accessories
 1x decoupling plate
 2x cable clamps R=25,6
 4x screws M4x25
 2x combi-screws M6x16
 2x screws M5x8

Surface filter color RAL 7001				Weight 7.7 kg		MCC201A5K5T3E20B		<i>Danfoss</i>	
B	06.10.2020	Besbes	306587	Scale 1:4.5	All Mode Sine-Wave Filter 6A 400V IP20				
A	06.10.2020	Besbes	306255						
Rev	Date	Name	Modification						
Cons.	06.10.2020	Besbes	General tolerance	ISO 2768-mK	Order number		Drawing Number-Revision-Version		
Draw.	06.10.2020	Besbes	ISO 5456		175U6006		186883-B-0		
Check.	06.10.2020	Eilers			Observe protection clause to ISO 16016			Sheet size	Sheet
								A4	1/1