



PE M6
Tightening torque: 6Nm





output terminals
U2, V2, W2: 50mm²
Tightening torque: 3.5-6.0Nm

input terminals
U1, V1, W1, R+: 16mm²
Tightening torque: 2.0-4.0Nm



A (1 : 2.5)



- included accessories**
- 1x decoupling plate
 - 1x cable clamp PUK 20B
 - 1x cable clamp PUK 40B
 - 2x cable clamps R=35
 - 4x screws M4x25
 - 2x combi-screws M6x16
 - 4x screws M5x8

Surface filter color RAL 7001				Weight 28.1 kg		MCC201A23KT3E20B	
B	06.10.2020	Besbes	306595	Scale 1:6	All Mode Sine-Wave Filter 24A 400V IP20		
A	06.10.2020	Besbes	306298				
Rev	Date	Name	Modification				
Cons.	06.10.2020	Besbes	General tolerance ISO 2768-mK	Order number 175U6024		Drawing Number-Revision-Version 209803-B-0	
Draw.	06.10.2020	Besbes	ISO 5456				
Check.	06.10.2020	Eilers		Observe protection clause to ISO 16016		Sheet size A4	Sheet 1/1



All Mode Sine-Wave Filter 24A 400V IP20

Observe protection clause to ISO 16016

Sheet size A4
Sheet 1/1