







X1 Mains 16mm²(3,5Nm)
 X2 Drive 16mm²(3,5Nm)
 X3/X4 Capacitor disconnect 10mm²(2,4Nm)
 A/B Temperature 2,5mm²(0,8Nm)



X1 Mains 16mm²(3,5Nm)
 X2 Drive 16mm²(3,5Nm)
 X3/X4 Capacitor disconnect 10mm²(2,4Nm)
 A/B Temperature 2,5mm²(0,8Nm)



		175C0492		VLТ Advanced Harmonic Filter AHF	
		Designation		X3 IP 20 with internal fan	
Drawn	2018-10-29	MK	Reviewed	2018-11-06	FR
Standard	DIN 2768-1 V		Scale drawing	1:1	
R3	DC fan + COG lifting eye	2018-10-02	FR	Print scale	Approx. 1:5
R2	Terminals	2016-03-14	FR	Drawing Number	
R1	Dimensions	2014-07-04	FR	X3-V3 IP20 if	
Status	Modifications	DATE	Name	1 A2	